

Movcam A7S Cage and Cage Kit Instruction Manual

STEP 1:

Grab your camera and cage or cage kit. If you have the cage kit, remove the riser block and Lightweight Support Base for now.



STEP 2:

Using a 2.5mm hex tool, carefully remove the screws holding the cage together. Note: There is not need to remove the top handle, we're simply demonstrating it can be removed. Also, the square side plate that connects to the top plate can stay as one piece.

#2



STEP 3:

Using a flathead screwdriver, secure the base of the cage to the bottom of the camera.

#3



STEP 4:

Return your camera to its upright position and grab your 2.5mm hex tool. Now find the piece of the cage with the HDMI protector. If it's not attached to the top plate, secure the two piece by inserting and tightening the two screws on the top.

#4



STEP 5:

Using the hex tool, reinsert the two screws in the side bracket and mount it to the base plate. One goes on the side and one on into the rounded corner. See #4 for a picture of where the screws go.

#5



STEP 6:

Attach the top handle by reinserting the two screws into the base of the handle.

#6



Movcam A7S Instructions Continued

Optional Parts and Accessories

STEP 7:

Attach the final curved piece by first placing the bottom peg into the hole in the base plate, then insert the bottom screw and fasten. The top prongs should fit perfectly into the top plate. Reinsert the final two screws along the top and tighten.

Optional Parts and Accessories

The Movcam A7S is compatible with other parts and accessories. Let's make the ultimate A7S Rig.

16x9 Inc. PL-E Adapter

169-CLM-PLE

Movcam A7S Riser Block

Comes with the Movcam Cage Kit and is ready to mount the 16x9 Inc. PL to E Adapter.

Movcam A7S Kit 1

Movcam Cage Kit [MOV-303-2200]
16x9 PL-E Adapter [169-CLM-PLE]
Movcam Rosette Adapter [MOV-303-1126]
Movcam 9" Dovetail [MOV-303-1706B]
2 8" Aluminum Rods [MOV-206-0003-5]

Movcam A7S Kit 2

Movcam Cage Kit [MOV-303-2200]
16x9 PL-E Adapter [169-CLM-PLE]
Movcam 9" Dovetail [MOV-303-1706B]
2 8" Aluminum Rods [MOV-206-0003-5]
MM4 Mattebox [MOV-301-0210]

Movcam A7S Shoulder Kit 1

Movcam Cage Kit [MOV-303-2200]
16x9 PL-E Adapter [169-CLM-PLE]
2 8" Aluminum Rods [MOV-206-0003-5]
Movcam Rosette Adapter [MOV-303-1126]
Pair of Anti Skid Hand Grips [MOV-303-1210]
Shoulder Pad [MOV-303-0219]
15mm Rod Clamp [MOV-303-0220]

Movcam A7S Shoulder Kit 2

Same as Shoulder Kit 1 without the Rosette Adapter and with the addition of the MM4 Mattebox [MOV-301-0210]

